







KEY FEATURES:

Ferrite

Subwoofer

- ① 560 W continuous program power capacity
- 2 95dB Sensitivity 1w/1m
- ③ 45 ~ 3200Hz frequency response range
- 4 High temperature copper wire wounded on polyimide former
- ⑤ Long glassfiber impregnated cone to provide outstanding reliability and performance
- 6 Ideal for compact 2-way systems


GENERAL SPECIFICATIONS			
Nominal Diameter	300mm /12inch		
Rated Impedan ce	4 ohm		
Nominal Power handling ¹	280 Watts		
Program Power ²	560 Watts		
Sensit ivity(1w/1m) ³	95 dB		
Frequency Range ⁴	45 ~ 3200Hz		
Minimum Impedan ce(Zmin)	4.5 ohm		
Voice Coil Diameter	65mm /2.5inch		
Voice Coil Material	Copper		
Former Material	Polyi mide		
Voice Coil Winding Depth	16 mm		
Number of layers	2		
Magnet gap depth	8 mm		
Basket	Pressed Steel		
Flux Density	1.06 T		
Magnet Outer Diameter / Wgt	156mm / 50 oz		


THIELE - SMALL PARAMETERS ⁵		
Resonance frequency	Fs	45 Hz
DC resistance	Re	3.6 ohm
Mechanical factor	Qms	12.4
Electrical factor	Qes	0.38
Total factor	Qts	0.37
Mechanical compliance	Cms	0.21mm/N
Mechanical resistance		
of suspension losses	Rms	1.38 mech-ohm
Effective Moving Mass	Mms	60 g
Half-space efficiency	Eff	1.9%
BL Factor	BL	12.7 T.m
Equival ent Cas air load	Vas	81 liters
Effective piston area	Sd	$0.0531\ m^2$
Max. linear excursi on ⁶	Xmax	6.5 mm
Voice coil inductance	Le1K	0.98 mH
Efficiency Bandwidth Product	EBP	118

MOUNTING INFORMATION		
Overall Diameter	311 mm	
Bolt Circle Diameter	294 mm	
Bolt Hole Diameter	6.5 mm	
Baffle Cutout Diameter	279 mm	
Overall Depth	127 mm	
Net Weight	4.3 kg	
Shipping Weight	5.0 kg	
Shipping Box	345x345x1 80 mm	

Also available in 8ohm, data upon request.







NOTES:

- 1. AES standard
- 2. Program Power is defined as 3 dB greater than the nominal power handling. 3. Sensitivity is measured at 1W input on rated impedance at 1m on axis.
- 4. Frequency range is defined as the band of frequencies delineated by the lower and upper limits where the output level drops by 10dB below the rated sensitivity
- 5. T/S parameters measured with laser system with a high level 25Hz sine wave preconditioning test.
- 6. The maximum linear excursion is calculated as: (Hvc-Hg)/2+Hg/4 where Hvc is the voice coil depth and
- Hg is the gap depth.
 7. Vb: Net internal volume of box after subtracting the volume of internal objects