※ 95.5 dB **※** 43 ~ 2900 Hz





KEY FEATURES:

- ① 500 W continuous program power capacity
- 2 95.5dB Sensitivity 1w/1m
- ③ 43 ~ 2900Hz frequency response range
- 4 Fiberglass former for increased rigidity and thermal protection
- ⑤ Long glassfiber impregnated cone to provide outstanding reliability and performance
- 6 Ideal for compact 2-way systems


GENERAL SPECIFICATIONS Nominal Diameter 380mm /15inch Rated Impedan ce 8 ohm Nominal Power handling 250 Watts Program Power² 500 Watts Sensitivity(1w/1m)3 95.5 dB Frequency Range⁴ $43 \sim 2900 Hz$ Minimum Impedan ce(Zmin) 7.1 ohm Voice Coil Diameter 50mm /2inch Voice Coil Material Copper **Fiber glass** Former Material Voice Coil Winding Depth 17 mm 2 Number of layers 8 mm Magnet gap depth Basket Pressed Steel Flux Density 1.1T Magnet Outer Diameter / Wgt 145mm / 42 oz


THIELE - SMALL PARAMETERS⁵		
Resonance frequency	Fs	43 Hz
DC resistance	Re	5.3 ohm
Mechanical factor	Qms	15
Electrical factor	Qes	0.78
Total factor	Qts	0.74
Mechanical compliance	Cms	0.13 mm/N
Mechanical resistance		
of suspension losses	Rms	1.83 mech-ohm
Effective Moving Mass	Mms	100 g
Half-space efficiency	Eff	1.4%
BL Factor	BL	13.6 T.m
Equival ent Cas air load	Vas	137 liters
Effective piston area	Sd	$0.0860 \ m^2$
Max. linear excursi on ⁶	Xmax	6.5 mm
Voice coil inductance	Le1K	1.27 mH
Efficiency Bandwidth Product	EBP	55

MOUNTING INFORMATION		
Overall Diameter	387 mm	
Bolt Circle Diameter	373 mm	
Bolt Hole Diameter	6.5 mm	
Baffle Cutout Diameter	355 mm	
Overall Depth	152 mm	
Net Weight	3.8 kg	
Shipping Weight	4.8 kg	
Shipping Box	420x420x2 05mm	

Also available in 4ohm, data upon request.







NOTES:

- 1. AES standard
- 2. Program Power is defined as 3dB greater than the nominal power handling 3. Sensitivity is measured at 1W input on rated impedance at 1m on axis.
- Frequency range is defined as the band of frequencies delineated by the lower and upper limits where the output level drops by 10dB below the rated sensitivity
- 5.T/S parameters measured with laser system without preconditioning test.
- 6. The maximum linear excursion is calculated as: (Hvc-Hg)/2+Hg/4 where Hvc is the voice coil depth and Hg is the gap depth.
 7. Vb: Net internal volume of box after subtracting the volume of internal objects